

技术参数 SPECIFICATIONS


- 线数 (Poles): 2~15(22)
- 适用线规 (Applicable wires): AWG28#~22#
- 适应基板厚度 (Applicable PC board thickness): 1.6mm
- 温度范围 (Temperature range): -25℃~85℃
- 额定电压 (Voltage rating): 250V.Ac/Dc
- 额定电流 (Current rating): 3A
- 接触电阻 (Contact resistance): ≤0.02Ω
- 绝缘电阻 (Insulation resistance): ≥1000MΩ
- 耐压 (Withstand voltage): 1000V.Ac/1min
- 材料 (Material):
 孔座 (Housing): 尼龙 (PA66) UL94V-2(0)
 针座 (Wafer): 尼龙 (PA66) UL94V-2(0)
 端子 (Terminal): 磷青铜 (Phos.bronze Tin/plated)




端子 TERMINAL(CH10)

型号 Type	适用线规 Applicable wires mm	AWG#	电线外径 O.D of wire ins mm	数量 Quantity
HX25410-PT	0.08~0.33	28~22	1.0~1.8	6000PCS/箱


HX25410-PT(CH10)




HX25410-Y(CH10)




HX25411-A(S045)



HX25411-WA(S045)



安装尺寸 MOUNTING MEASUREMENT



孔座 HOUSING(CH10)

线数 Poles	型号 Type	尺寸 Dimensions(mm)
		A B
2	HX25410-2Y	2.54 5.56
3	HX25410-3Y	5.08 8.10
4	HX25410-4Y	7.62 10.64
5	HX25410-5Y	10.16 13.18
6	HX25410-6Y	12.70 15.72
7	HX25410-7Y	15.24 18.26
8	HX25410-8Y	17.78 20.80
9	HX25410-9Y	20.32 23.34
10	HX25410-10Y	22.86 25.88
11	HX25410-11Y	25.40 28.42
12	HX25410-12Y	27.94 30.96
13	HX25410-13Y	30.48 33.50
14	HX25410-14Y	33.02 36.04
15	HX25410-15Y	35.56 38.58
...
22	HX25410-22Y	53.34 56.36

针座 WAFER(S045)

线数 Poles	型号 Type 直式(180°)	尺寸 Dimensions(mm)
		A B
2	HX25411-2A/WA	2.54 5.08
3	HX25411-3A/WA	5.08 7.62
4	HX25411-4A/WA	7.62 10.16
5	HX25411-5A/WA	10.16 12.70
6	HX25411-6A/WA	12.70 15.24
7	HX25411-7A/WA	15.24 17.78
8	HX25411-8A/WA	17.78 20.32
9	HX25411-9A/WA	20.32 22.86
10	HX25411-10A/WA	22.86 25.40
11	HX25411-11A/WA	25.40 27.94
12	HX25411-12A/WA	27.94 30.48
13	HX25411-13A/WA	30.48 33.02
14	HX25411-14A/WA	33.02 35.56
15	HX25411-15A/WA	35.56 38.10
...
22	HX25411-22A/WA	53.34 55.88