



SPEC. A-A



SPECIFICATIONS

Current Rating:1A AC/DC
Pitch Between Poles:1.25mm
Votlag rating:125V AC/DC
Contact Resistance:20MΩ max
Temperature Range:-25℃ TO +85℃
Insulation Resistance:100MΩ min
Withstand Voltage:500V AC/minute

MATERIAL

Material:Nylon66 UL94V-2

Poles	Part No.	Dimension mm		
		A	B	C
2	1251H-2P	4.25	1.25	2.95
3	1251H-3P	5.50	2.50	4.20
4	1251H-4P	6.75	3.75	5.45
5	1251H-5P	8.00	5.00	6.70
6	1251H-6P	9.25	6.25	7.95
7	1251H-7P	10.50	7.50	9.20
8	1251H-8P	11.75	8.75	10.45
9	1251H-9P	13.00	10.00	11.70
10	1251H-10P	14.25	11.25	12.95
11	1251H-11P	15.50	12.50	14.20
12	1251H-12P	16.75	13.75	15.45
13	1251H-13P	18.00	15.00	16.70
14	1251H-14P	19.25	16.25	17.95
15	1251H-15P	20.50	17.50	19.20
16	1251H-16P	21.75	18.75	20.45

APPROVED:		DATE:		C kmtw CHANKLEMENT INDSTRYCO., LTD 深圳市灿科盟实业有限公司				
CHECKED:		DATE:		TITLE:				
				1251H-XP				
TOLERANCE TABLE				CLIENT P/N /				
.0 ±0.20				UNIT mm		SCALE free	⌀	≡
.00 ±0.10		DRAWN:		DATE:				
.000 ±0.05		LYF		2008-04-07		FILE NO. Ckmtw-1251-0005		REV. A