


Description



Catelogy:	Anti-static Tweezers	Model:	BST-ESD-10
Material:	302stainless steel	Brand:	BEST
Magnetism:	Non	Strength:	>HRC40°
Size:	117mm	Weight:	25g
Feature1:	Anti-magnetic,anti-acid,hard,excellent toughness		
Feature2:	Polished and sandblasted matte treatment		
Featuer3:	Side handle is polished ,easy to use		
Feature4:	Suitable for PCB semiconductor, photovoltaic and other		

Size



Picture

Side



Side



Top



Pack



Details



Stainless steel tweezers, Tail polished, no scratches, flawless surface



Using high-precision equipment screen printing, legible



When two tip are folded, smooth seamless

Description

Category:	Anti-static Tweezer
Model:	BST-ESD-10
Material:	302Stainless steel
Magnetism:	Non
Surface treatment:	Black anti-static coating treatment
Tip strength:	>HRC40°
Length:	117mm
Weight:	25g(with package)
Packing:	20pc/box
Weight/box:	589g
Size of box:	204*163*45 (L*W*H)
Size of carton:	500*340*430mm (L*W*H)
Weight of carton:	16.3kg