

## EP-505



EP-405



EP-505



EP-605

### EP系列 可调恒温电烙铁 规格可选

| 型号   | EP-405       | EP-505       | EP-605       |
|------|--------------|--------------|--------------|
| 额定功率 | 50W          | 50W          | 50W          |
| 电源电压 | 220V~50Hz    | 220V~50Hz    | 220V~50Hz    |
| 电气强度 | 3750V 1分钟不击穿 | 3750V 1分钟不击穿 | 3750V 1分钟不击穿 |
| 调温范围 | 200~450°C    | 200~450°C    | 200~450°C    |
| 产品净重 | 200g         | 340g         | 346g         |