

EP-405



EP-405



EP-505



EP-605

EP系列 可调恒温电烙铁 规格可选

型号	EP-405	EP-505	EP-605
额定功率	50W	50W	50W
电源电压	220V~50Hz	220V~50Hz	220V~50Hz
电气强度	3750V 1分钟不击穿	3750V 1分钟不击穿	3750V 1分钟不击穿
调温范围	200~450°C	200~450°C	200~450°C
产品净重	200g	340g	346g