



特征:

1、电气特性:

- A: 250伏特AC最大2安培介值耐电压伏特数
- B: 500伏特AC耐压比
- C: 500万欧姆绝缘电阻
- D: 最大35万欧姆终端电阻

2、机械特性:

- A: 拉力测试--- 电缆至插座张力强度至少20磅 (89N)
- B: 耐力测试--- 插拔测试1000次

FEATURES:

1 Electrical Test:

- A. 250V AC max at 2 amps.
- B. Dielectric with standing 500volts AC.
- C. Insulation Resistance:500 megaohms.
- D. Termination Resistance:35megaohms.

2 Mechanical:

- A. Cable-to-Plug tensile strength-20lbs (89N)min.
- B. Durability:1000 mating cycles.

For standard Wire

8p8c 六类一件式1.1孔(三爪)水晶头

深圳市安普达网络科技有限公司 SHENZHEN ANPUDA NETWORK TECHNOLOGY CO., LTD		FILE NAME	MATERIAL	UNIT	MATERIAL ON	EDITION	G/A
DRAWN	APPROVED	MOLDING ON	PC/金壳	MM			
			DECIMALS	.XX=±0.1 .XXX=±0.05	ANGLES	.XX°=±0.1°	
			CONTRACTION		EFFECTIVE DATE	2015.6.4	