



NOTE:
 Rating: DC 30V 0.1A
 Operating Force: 20 ± 10 gf
 Lifetime: 50,000 Cycles

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Contact Spring	—	1	Be Alloy	Ag Plated	—
④	Terminal	—	2	Phosphor Bronze	Ag Plated	—
③	Cover	—	1	SUS	Natural	—
②	Housing	—	1	LCP	Black	—
①	Slider	—	1	PA46	Black	—

APPROVALS		DATE	TITLE:	
DRAWN	J.X.Zhang	2013/8/26	DETECTOR SWITCHES	
CHECKED			ELECTRONICS CO.,LTD	
APPROVALS			K5-1617SA-04	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
TOLERANCES ARE			30~12.5 ±0.30	10~30 ±0.20	5~10 ±0.15	~5 ±0.10
			ANGLE	±2'	DRAWING NO.	
			UNIT: mm	SCALE: 1:1	PROJ:	
			SHEET 1 OF 1			