



NOTE:
 Rating: DC 12V 50mA
 Operating Force: 30±10gf
 Lifetime: 100,000 Cycles

	PART NO.	K5-1620UA-01
		K5-1620UN-01
		K5-1620UN-01

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Contact Spring	---	1	Phosphor Bronze	Ag Plated	---
④	Terminal	---	4	Phosphor Bronze	Ag Plated	---
③	Base	---	1	PA46	Black	---
②	Cover	---	1	SUS	Natural	---
①	Slider	---	1	PA46	Black	---

DRAWN		J.X.Zhang	DATE		2013/8/28	TITLE:		DETECTOR SWITCHES	
CHECKED			APPROVALS			PART NO.			
APPROVALS			TOLERANCES ARE		30~12.5 ±0.30 10~30 ±0.20 5~10 ±0.15 ~5 ±0.10	ANGLE		±2°	
ECN NO.	REV.	DATE.	DESCRIPTION.		NEW	CHANGE.	CHECK.	APPRO.	SCALE: 1:1
	A								PROJ:
									SHEET 1 OF 1



ELECTRONICS CO., LTD