


CIRCUIT DIRGRAM



HOLE LAYOUT

NOTE:  
 Rating: DC 30V 0.1A  
 Operating Force: 50±10gf  
 Lifetime: 50,000 Cycles

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Spring	—	1	Beryllium copper	Ag Plated	—
④	Terminal	—	2	Phosphor Bronze	Ag Plated	—
③	Base	—	1	NYLON	Black	—
②	Cover	—	1	NYLON	Black	—
①	Slider	—	1	NYLON	Black	—

APPROVALS		DATE	TITLE:	
DRAWN	J.X.Zhang	2013/9/23	DETECTOR SWITCHS	
CHECKED			ELECTRONICS CO.,LTD	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	ANGLE	UNIT:	SCALE:	PROJ:	SHEET
	A		NEW				30~12.5 ±0.30	±2°	mm	1:1	PROJ: 1630DA-01	1 OF 1
							10~30 ±0.20					
							5~10 ±0.15					
							~5 ±0.10					