



PCB Layout(Pattern side)

NOTE:
Operating Force: 40gf Max

⑥	Terminal	—	3	Phosphor Bronze	Ag Plated	—
⑤	Housing	—	1	PA46	Black	—
④	Contact Spring	—	1	Be Alloy	Ag Plated	—
③	Frisket	—	1	PA46	Black	—
②	Cover	—	1	SUS	Natural	—
①	Slider	—	1	PA46	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		 ELECTRONICS CO.,LTD		
DRAWN	J.X.Zhang	2013/9/3				
CHECKED				TITLE: DETECTOR SWITCHES		
APPROVALS				PART NO. K5-1639SN-01		
TOLERANCES ARE			30~以下	±0.30	ANGLE	UNIT: mm
			10~30	±0.20		
			5~10	±0.15		
			~ 5	±0.10		
		±2'		SCALE: 1:1		PROJ:
DRAWING NO.				SHEET 1 OF 1		

—	A	—	NEW	—	—	—
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.