



全T. P. R防滑塑胶料和P. P耐冲击塑料，双色制造

符合人体工学设计
具有扭力释放效果

采用镍铬钼合金钢制造
金属杆直径6.0mm

前端染黑加硬处理，硬度高，
耐磨损，不滑牙，附强磁，
十字头型#2




58mm

















工作长度
40mm



型号	杆长	起子直径	柄长	全长	包装方式
9SD-220B	40mm	⊕ #2	58mm	98mm	内盒



型号	A	B	C	D	E
9SD-201B	75	⊕ #0	88	3.0	163
9SD-202B	75	⊕ #1	109	5.0	184
9SD-205B	100	⊕ #0	88	3.0	188
9SD-207B	100	⊕ #2	121	6.0	221
9SD-210B	100	⊕ #1	109	5.0	209
9SD-213B	150	⊕ #2	121	6.0	271
9SD-214B	200	⊕ #2	121	6.0	321
9SD-216B	150	⊕ #1	109	5.0	259
9SD-217B	250	⊕ #2	121	6.0	371
9SD-220B	40	⊕ #2	58	6.0	98
9SD-222B	150	⊕ #3	121	8.0	271

9SD-201A	75		3.0	88	3.0	163
9SD-202A	75		5.0	109	5.0	184
9SD-205A	100		3.0	88	3.0	188
9SD-207A	100		6.0	121	6.0	221
9SD-210A	100		5.0	109	5.0	209
9SD-213A	150		6.0	121	6.0	271
9SD-214A	200		6.0	121	6.0	321
9SD-220A	40		6.0	58	6.0	98
9SD-222A	150		8.0	121	8.0	271
9SD-200-T05H	50		T05H	88	3.0	138
9SD-200-T06H	50		T06H	88	3.0	138
9SD-200-T07H	50		T07H	88	3.0	138
9SD-200-T08H	50		T08H	88	3.0	138
9SD-200-T09H	50		T09H	88	3.0	138
9SD-200-T10H	75		T10H	88	3.0	163
9SD-200-T15H	75		T15H	88	4.0	163