



夹持功能

剥线范围: AWG:18,16,14,12,10/0.9,
1.25,2.0, 3.5, 5.5 mm²

剥线准确快速, 适用一般较粗电线

剪切, 刀口锋利

低碳钢材质

硬度: HR30N 55° ~65°

压接口设计



弹簧设计

PVC防滑手柄, 握感舒适





170mm

型号	材质	硬度	剥线范围	全长 (mm)	包装方式
8PK-3161	低碳钢	HR30N 55°~65°	AWG: 18, 16, 14, 12, 10 / 0.9, 1.25, 2.0, 3.5, 5.5 mm ²	170	泡壳 卡片



夹持/剥线/剪切

本体采用低碳钢材质制成, 硬度 HR30N: 55°~65°, 刀刃加硬处理及研磨, 铣床加工, 钳口具夹持设计, 方便操作
剥线范围: AWG:18,16,14,12,10 (0.9,1.25,2.0,3.5,5.5mm²)



压接功能

本品具有压接功能，方便操作



弹簧设计

弹簧设计，可自动打开钳口，方便省力

舒适手柄

优质PVC手柄，握感舒适，方便存取拿放



