


规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V/50-60Hz) 60S min.
操作力 Operation force	≤180±30gf / ≥250±50gf
寿命试验 Operating Life	50,000 cycles / 30,000 cycles
行程 Travels	0.25±0.1mm



RECOMMENDED P.C.B. LAYOUT  
安装尺寸图

**PRODUCT NO. : 1T5002\*\*\*\*\*-CT**

轻触开关  
3X6系列

外形:  
A=插脚  
B=贴片  
C=贴片带柱  
K=贴片带柱8.8  
L=贴片10.2

按钮颜色:  
底座颜色:  
盖板颜色:  
操作力度:  
130=130gf  
160=160gf  
180=180gf  
250=250gf  
300=300gf

初始颜色:  
则不启用

材质:  
0=初始材质  
1=新增材质  
依次增加

产品高度 (H):  
350=3.5mm  
370=3.7mm

编带  
非编带, 不启用

手感:  
0=带规  
1=大手感  
2=小手感  
3=特殊手感

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	COVER	1	STAINLESS STEEL	/
4	ACTUATOR	1	LCP	BLACK
3	DOME	1	STAINLESS STEEL	AG-PLATED
2	TERMINAL	2	BRASS	AG-PLATED
1	HOUSING	1	LCP	YELLOW

UNITS	MM	NAME(INTENDED USE)	HON YUAN
X. ± 0.3	X. ± 3'	3X6 SMT SERIES	HON YUAN PRECISION IND. CO.,LTD.
X. ± 0.2	X. ± 2'	TACT SWITCH	SHENZHEN, CHINA, R.O.C.
.XX ± 0.1	.XX' ± 1'	PART NO.(INTENDED USE)	
.XXX ± 0.05	.XXX' ± 0.5'	ITS002G****-*****-CT*0	

APPD: ZO 5/22/2014	DWG NO.: 1T5002G
CHKD: M.H.LI 5/22/2014	SCALE SHEET REV.
DR: WP.LU 5/21/2014	10/1 1/1 A

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.