



一. 电气性能:

- 1-1. 额定电流: 3A AC DC.
- 1-2. 接触电阻:  $\leq 20m\Omega$
- 1-3. 绝缘电阻:  $\geq 1000M\Omega$
- 1-4. 耐压: 550V AC/Minute

二. 物理特性:

- 2-1. 操作温度:  $-55^{\circ}C \sim 105^{\circ}C$
- 2-2. 焊接温度:  $+220^{\circ}C$ , 10s max

三. 材质:

- 3-1. 塑胶: PBT (Black) UL94V-0
- 3-2. 插针: Brass/Gold plated

Pin	A	B
1	2.00	0.00
2	4.00	2.00
3	6.00	4.00
4	8.00	6.00
5	10.00	8.00
6	12.00	10.00
7	14.00	12.00
8	16.00	14.00
9	18.00	16.00
10	20.00	18.00
11	22.00	20.00
12	24.00	22.00
13	26.00	24.00
14	28.00	26.00
15	30.00	28.00
16	32.00	30.00
17	34.00	32.00
18	36.00	34.00
19	38.00	36.00
20	40.00	38.00
21	42.00	40.00
22	44.00	42.00
23	46.00	44.00
24	48.00	46.00
25	50.00	48.00
26	52.00	50.00
27	54.00	52.00
28	56.00	54.00
29	58.00	56.00
30	60.00	58.00
31	62.00	60.00
32	64.00	62.00
33	66.00	64.00
34	68.00	66.00
35	70.00	68.00
36	72.00	70.00
37	74.00	72.00
38	76.00	74.00
39	78.00	76.00
40	80.00	78.00

图名:	PZ2. 0-1xNA-L8. 7MM			未标注公差		绘制:	韩金锋	单位:	MM
	XX.	$\pm 0.40$	XX.°	$\pm 2^{\circ}$					
图号:	XXXXXXXXXXXXXXXXXXXXXXXXXXXX			X.	$\pm 0.30$	XX.°	$\pm 1^{\circ}$	签发:	比例:
	XXXXXXXXXXXXXXXXXXXXXXXXXXXX			.XX	$\pm 0.20$			审核:	
				$\pm 0.15$				视图:	