


37P	54.84	63.50	69.32	7.90	12.50
25P	38.38	47.04	53.04	7.90	12.50
15P	24.66	33.32	39.14	7.90	12.50
9P	16.33	24.99	30.81	7.90	12.50
PDS. NO.	A	B	C	D	E
	DIMENSION				



SPECIFICATIONS:

Current rating:3.0A AC/DC
 Voltage rating:250V AC/DC
 Contact resistance:30m ohm MAX
 Insulation resistance:5000M ohm MIN
 Withstanding voltage:1000V AC for one minute
 Operating temperature range:-40°C~+85°C

MATERIAL AND FINISH

Insulator:PBT+30%G.F<UL94V-0>
 Contact:Copper Alloy Nickel Undercoated
 Selective Gold Plated
 Finish:Metal Iron With Tin Plated

PART NO.:

Z-SUB DP * F * 0 * * * * *

NO. OF CONTACTS ————
 A=9PIN
 B=15PIN
 C=25PIN
 E=37PIN

MOUNTING OPTIONS ————
 1=RIVETED W/SHIELD ONLY
 2=RIVETED W/FRONT RIVET
 3=RIVETED W/REAR RIVET
 4=RIVETED W/NUT RIVET
 5=RIVETED W/HEX SCREW +HEX NUT

CONTACT MATERIAL ————
 7=PHOSPHOR BRONAE

LOGO
 0=NO LOGO
 2=NEXTRON

INSULATOR COLOR ————
 0=BLACK
 6=BLUE
 9=WHITE

INSULATOR MATERIAL ————
 0=PBT
 2=NYLON

CONTACT PLATED:(CONTACT AREA)
 1=FULL GOLD 1u"
 2=GOLD 3u"
 3=GOLD 5u"
 5=GOLD 15u"
 6=GOLD 30u"

正凌精密工业(广东)有限公司
 内部资料请勿复印

B1	MARK MODIFY =1	12/7'16
B	ECN-150091 UPDATE	7/27'15
A	NEW RELEASED	11/13'09
REV.	DESCRIPTION	DATE

UNITS ■mm □INCH	NAME: D-SUB DP TYPE FEMALE PCB SOLDER TYPE	 NEXTRONICS ENGINEERING CORP.	
GENERAL TOLERANCES: (UNLESS SPECIFIED)	PART NO: Z-SUBDP*F*0******	TITLE: CUSTOMER DWG	
	APPD: 楊海文	DWG NO: 010-0000-636	
	CHKD: 廖小瓊	C	
	DRAWN: 陳惠枝 2016/11/15	SCALE:	SHEET: 1/1
		REV.:	B1