


NOTE
 MATERIAL & FINISH
 INSULATOR: PBT/PA9T<STD> 30%G.F <UL94V-0>
 CONTACT MATERAIL: BRASS
 CONTACT PLATING: Au OR Sn OVER Ni

ELECTRICAL & MECHANICAL
 CURRENT RATING: 3.0A
 CONTACT RESISTANCE: 20mΩ MAX.
 INSULATION RESISTANCE: 1000MΩ MIN.
 WITHSTAND VOLTAGE: 1000V AC/DC
 OPERATION TEMPERATURE: -40°C TO +105°C



PART NO. Z-S3110**R**K0*

NO.OF PINS

| | |
|-----|-----|
| 6P | 24P |
| 8P | 26P |
| 10P | 30P |
| 12P | 34P |
| 14P | 40P |
| 16P | 50P |
| 18P | 60P |
| 20P | 64P |


PACKING
 A=TRAY
 T=TUBE

COLOR
 G=GRAY(427C)
 E=GRAY(413C)
 B=BLACK
 U=BLUE

PLATING
 0=TIN
 1=GOLD FLASH
 4=GOLD 10U"
 5=GOLD 15U"
 6=GOLD 30U"

7=GOLD FLASH/TIN
 A=GOLD 10U"/TIN
 B=GOLD 15U"/TIN
 C=GOLD 30U"/TIN

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



| NO.PIN | L |
|---------|------|
| 6P-8P | 4.00 |
| 10P-64P | 4.40 |

正凌精密工业(广东)有限公司
 2016/4/5
 内部资料请勿复印

| REV. | DESCRIPTION | DATE |
|------|-------------------|--------|
| A1 | MODIFY $\Delta=1$ | 4/1'16 |
| A | NEW RELEASED | 3/4'16 |

| UNITS | NAME: | nexttron® NEXTRONICS ENGINEERING CORP. | | |
|---|-----------------------------|---|-----|--|
| mm INCH | 2.54 BOX HEADER 90° H=9.0 | TITLE: CUSTOMER DWG | | |
| GENERAL TOLERANCES: (UNLESS SPECIFIED) | PART NO: Z-S3110**R**K0* | DWG NO: 010-0000-F30 | | |
| 4 PLACE ±** ±** | APPD: 楊海文 2016/4/5 | SCALE: SHEET: REV.: | | |
| 3 PLACE ±0.15 ±.** | CHKD: 廖小瓊 2016/4/5 | 4/1 | 1/1 | |
| 2 PLACE ±0.25 ±.** | DRAWN: 陳惠枝 2016/4/5 | A1 | | |
| 1 PLACE ±0.40 ±.** | | | | |
| ANGULAR: X°±3° .X°±** | | | | |