

NOTES:
 Current Rating:1.5AMP
 Contact Resistance:20mΩ max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ min
 Operation Temperature:-40℃ to +105℃

Contact Material:Brass
 Contact plating:Au or Sn Over Ni
 Insulator Material:PA9T+30%GF(UL94V-0)

PART NO.

Z-S973111 ** R * * K * 1


No. of Pins
 10P, 14P, 16P,
 20P, 24P, 26P,
 30P, 34P, 40P,
 44P, 50P, 60P,

Packing
 A=Tray
 T=Tube



PLATING

0=TIN
 1=GOLD FLASH
 2=GOLD 3U"
 3=GOLD 5U"
 4=GOLD 10U"
 5=GOLD 15U"
 6=GOLD 30U"
 7=GOLD FLASH/TIN
 8=GOLD 3U"/TIN
 9=GOLD 5U"/TIN
 A=GOLD 10U"/TIN
 B=GOLD 15U"/TIN
 C=GOLD 30U"/TIN

Color Insulator
 B=Black
 U=Blue
 W=White



Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



A	NEW RELEASED	1/8'16	
REV.	DESCRIPTION	DATE	APPD

UNITS <input checked="" type="checkbox"/> mm <input type="checkbox"/> INCH	NAME: 2.00 BOX HEADER 90° H=5.7	NEXTRONICS ENGINEERING CORP.	
GENERAL TOLERANCES: (UNLESS SPECIFIED)	PART NO: Z-S973111**R**K*1	TITLE: CUSTOMER DWG	
	APPD:	DWG NO: ****	C
	CHKD:	SCALE: 4 / 1	SHEET: 1 / 1
	DRAWN: 陳惠枝 1/8'16	REV.:	A
ANGULAR: X°±3° X'±**			