

NOTE
 MATERIAL & FINISH
 INSULATOR: PA9T 30%GF (UL94 V-0)
 CONTACT: BRASS, GOLD OR TIN OVER NI

ELECTRICAL & MECHANICAL
 CURRENT RATING: 1.5A
 CONTACT RESISTANCE: 20mΩ MAX.
 INSULATION RESISTANCE: 1000MΩ MIN.
 WITHSTAND VOLTAGE: 500V AC/DC
 OPERATION TEMPERATURE: -40°C TO +105°C

PART NO.
 Z-S973111 ** S * * * 01


NO.OF PINS
 10P、14P、16P、
 20P、24P、26P、
 30P、34P、40P、
 44P、50P、60P、

PACKING
 A=TRAY
 T=TUBE

PLATING
 0=TIN
 1=GOLD FLASH
 2=GOLD 3U"
 3=GOLD 5U"
 4=GOLD 10U"
 5=GOLD 15U"
 6=GOLD 30U"
 7=GOLD FLASH/TIN
 8=GOLD 3U"/TIN
 9=GOLD 5U"/TIN
 A=GOLD 10U"/TIN
 B=GOLD 15U"/TIN
 C=GOLD 30U"/TIN

INSULATOR COLOR
 B=BLACK
 U=BLUE
 W=WHITE

Recommended P.C.B Layout(Top Side)
 (PCB BOARD TOLERANCE±0.05)



正凌精密工业(广东)有限公司
 2016/5/11
 内部资料请勿复印

REV.	DESCRIPTION	DATE
A	NEW RELEASED	5/4/16

UNITS ■mm □INCH		NAME: 2.00 BOX HEADER 180° H=5.7
GENERAL TOLERANCES: (UNLESS SPECIFIED)		PART NO: Z-S973111**S***01
	mm	INCH
4 PLACE	± **	± **
3 PLACE	± 0.15	± **
2 PLACE	± 0.25	± **
1 PLACE	± 0.40	± **
ANGULAR:	X°±3°	.X°±**

APPD: 楊海文
2016/5/10

CHKD: 廖小瓊
2016/5/9

DRAWN: 陳惠枝
2016/5/5

 NEXTRONICS ENGINEERING CORP.		TITLE: CUSTOMER DWG
DWG NO: 010-0000-F82		C
SCALE: 4/1	SHEET: 1/1	REV.: A