



HOLE LAYOUT ± 0.05



CIRCUIT DIAGRAM
C: COMMON PIN
BOTTOM VIEW



Specifications:

Contact rating:	0.1A, 12V DC
Contact resistance:	20mOhm max.
Insulation resistance:	100MOhm min. at 500V DC for 1 minute
Dielectric strength:	500V AC (50/60Hz, 2mA) for 1 minute
Operating temperature:	-25°C to +85°C
Mechanical life:	10 000 cycles
Operating force:	250 +/-100gf
Soldering conditions:	260 +/-5°C, 5 +/-1sec.
Material:	Contact clip: phosphor bronze, silver plated Slider: POM, black Spring plate: phosphor bronze, washing Terminal: brass strip, silver plated Base: phenolic resin, natural Frame: steel, tin plated



Tolerances: up to 10: ±0.2mm above 10-50: ±0.3mm	Date	Name
	04/10	dr
Operating temperature	07/13	dr
Modifications	Date	Name

MFP 213 N

30 20 58

Page

1/1

knitter-switch