



Specifications:

- Contact rating: 30V DC, 300mA
- Contact resistance: <50mOhm
- Insulation resistance: >100MOhm at 500V DC
- Dielectric strength: 500V, 50Hz for the duration of 1 minute
- Mechanical life: min. 5000 operations
- Contacts: phosphor bronze, silver plated
- Terminals: brass, silver plated
- Contact timing: non-shorting
- Slide colour: black
- Soldering conditions: auto-soldering: 260°C, 5sec. max.
- Switching function: on - on

Maßstab		Datum	Name	<h1>MMP 122-R</h1>
Oberfläche		09/05	dr	
		knitter-switch		<h2>30 07 00</h2>
Zust	Änderung	Datum	Name	Blatt 1/1