








PB-05

受控文件



Rating: 3A 125V AC
 Contact Resistance: 50mΩ Max.
 Insulation Resistance:DC 500V 100MΩ Min.
 Dielectric Strength:AC 1000V 1 minute
 Total travel:1.4±0.4mm
 Operating Force:200±50gf
 Operating Life:10,000 cycles
 Operating Temperature:0°C~85°C

Function: OFF - (ON)



Panel Thickness: 3mm MAX.

MATERIAL:
 Base: Brass, Ni plated ;
 Cap: ABS ;
 Terminal: Copper, Silver or Tin plated ;
 Nut: Brass, Ni plated .

CUT-OUT

Y	Yellow	黄色
W	White	白色
U	Blue	蓝色
R	Red	红色
O	Orange	橙色
G	Green	绿色
B	Black	黑色
A	Gray	灰色
CAP COLOR (X)		

公差 TOLERANCES		.X± 0.3	.XX± 0.15	角度 ANGLE± 1°	单位 DIMENSION UNIT	mm.
版本 VERSION		A1	比例尺 SCALE		品名 TITLE	
核 准 APPROVED BY		李新超	核 对 CHECKED BY		图 号 DRAWING NO	
日期 DATE		2008.07.08	日期 DATE		PB-05-B-X	
ECN NO.		N/A	绘图 DRAWN BY		PB-05-B-X_A1	
变更说明 CHANGE DESCRIPTION		2008.07.08	姜庆勇			
图纸重新整理发行		2009.09.15	李伟奇			
New Issue		2008.07.08	姜庆勇			
版本 VER		2008.07.08	姜庆勇			