






东莞市宏聚电子五金制品有限公司



HONGJU(DONGGUAN)ELECTRONIC & METAL PRODUCTS CO.,LTD

# PB-10A



Rating: 3A 125V AC ;  
 Contact Resistance: 50mΩ Max. ;  
 Insulation Resistance:DC 500V 100MΩ Min. ;  
 Dielectric Strength:AC 1000V 1 minute  
 Total Travel: 3.0±0.5mm  
 Operating Force:350±100gf  
 Electrical Life:10,000 cycles  
 Operating Temperature:0°C~85°C

### CUT-OUT



**MATERIAL:**  
 Body: Nylon66, UL rated:94V-2 min  
 Actuator: ABS, UL rated:94V-2 min  
 Terminal: Brass with silver-plate

Y	Yellow 黄色
W	White 白色
U	Blue 蓝色
R	Red 红色
O	Orange 橙色
G	Green 绿色
B	Black 黑色
A	Gray 灰色

BASE COLOR (X) CAP COLOR (X)

公差 TOLERANCES		.X±0.3		.XX±0.15		角度 ANGLE ± 1°	
版本 VERSION	A0	比例尺 SCALE	NONE	日期 DATE	2014.07.09	品名 TITLE	PB-10A-XX
核准 APPROVED BY		核对 CHECKED BY		绘图 DRAWN BY		图号 DRAWING NO	PB-10A_A1
版本 VER	A1	重新整理发行 CHANGE DESCRIPTION		日期 DATE	2014.07.09	ECN NO.	N/A