

XKB



SPECIFICATIONS

1. ELECTRICAL

● Contact rating	0.1A, 30VDC
● Contact resistance	50mWMax.
● Insulation resistance	100MΩMin. at 250VDC
● Dielectric strength	250VAC Min. for 60 sec.

SWITCH CONNECTOR

2P ON-OFF



ΔX					ANGLAR	±5°	DSND		DATE		SCALE: N/A	MODEL TYPE:	
ΔX					L ≤ 4	±0.2	DWN		DATE		VIEW:	PUSH SWITCH	
ΔX					4 < L ≤ 16	±0.3	CHKD		DATE		UNIT: mm	PART NO.:	
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4	APPD		DATE		SIZE: A4	DWG NO.:	
					L > 63	±0.5						XKB11E01	
REVISIONS					UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT	SHEET	REVISION
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn											1.0g	1/1	A0