


主要技术性能		公差
额定电负荷	DC 30V\3.0A	X.±0.20
接触电阻	≤0.03Ω	.X±0.10
绝缘电阻	≥100MΩ	.XX±0.05
耐压	AC500V(50Hz)/min	.XXX±0.02
插拔力	3-20N	X°±5°
使用温度范围	-30~70℃	.X°±2°
使用寿命	5000次	.XX±1°



P. C. B LAYOUT TOP VIEW

	MATERIAL	PLATING
center pin	brass	nickel
terminal 1	brass	silver
terminal 2	copper alloy	silver
terminal 3	brass	silver
plastic	PBT	

REVISIONS					UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				
△X					ANGLAR	±5°	DSND		DATE	SCALE: N/A	MODEL TYPE: DC POWER JACK
△X					L ≤ 4	±0.2	DWN		DATE	VIEW:	PART NO.:
△X					4 < L ≤ 16	±0.3	CHKD		DATE	UNIT: mm	DWG NO.:
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4	APPD		DATE	SIZE: A4	DC-044A-2.5A-2.5
					L > 63	±0.5					WEIGHT
											1.0g
											SHEET
											1/1
											REVISION
											A0