



Notes:

1. Dimension shall be interpreted per ASME Y14.5M1994.
2. Dimension marked ∇ & \blacktriangledown should be checked by Q.C. and process, engineers and ∇ should also check the CPK data.

Specification:

1. Current Rating: 1.8 AMP
2. Voltage Rating: 30V AC,DC
3. Dielectric Strength: 500V AC RMS for 1 minute.
4. Contact Resistance: 30 mΩ Max.
5. Insulator Resistance: 500M Ω Min. AT 250V DC.
6. Mating/Unmating cycles: 5000cycles
7. Temperature: -30°C to +80°C

P. C. B LAYOUT

SWITCH CONNECTOR

					DSND		DATE		SCALE: N/A	MODEL TYPE: USB		
					DWN		DATE		VIEW:	PART NO.:		
					CHKD		DATE		UNIT: mm	DWG NO.: U-E-M1SS-W-2		
					APPD		DATE		SIZE: A4	WEIGHT	SHEET	REVISION
					UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED		
MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°						
ΔX					L ≤ 4	±0.2						
ΔX					4 < L ≤ 16	±0.3						
ΔX					16 < L ≤ 63	±0.4						
					L > 63	±0.5						
REVISIONS												
www.xk-dg.cn www.1k0k.com www.1k0k.cn												