



- NOTES:
- MATERIAL:
 - HOUSING: 'BLANK' = NYLON 6/6, UL94V-2, COLOR: NATURAL
 - '201' = NYLON 6/6, UL94V-0, COLOR: NATURAL
 - TERMINAL: C2700W BRASS
 - FINISH: 0.000003/(.0000001) MIN. TIN OVERALL OVER
0.000001/(.00000004) MIN. NICKEL OVERALL
 - PRODUCT SPECIFICATION: NONE
 - PACKAGING: PK-5219-002
 - MATES WITH: 3191-02R SERIES
 - DIFFERENCE OF DIMENSION IS INTENTIONAL TO PREVENT PART RISING FROM P.C.B.
 - PARTS CONFORM TO CLASS 'B' REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.

ENG. NO.	ORDER NO.	PIN STYLE	HSG. MATERIAL	PIN PLATING
5219-02A	15-31-1026	SOLID	94V-2 NYLON	TIN
5219-02C	15-31-3026	HOLLOW	94V-2 NYLON	TIN
5219-02A-201	39-28-7028	SOLID	94V-0 NYLON	TIN
5219-02AG-201	39-33-9021	SOLID	94V-0 NYLON	GOLD

ADD P/N 15-31-3026 EC NO: UCP2014-1950 DRW:NAELHAG 2013/11/06 CHKD:JBELL 2013/11/06 APPR:FSMITH 2013/12/19 N5	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE MM ONLY	SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION
	▽=0	mm INCH	DRAWN BY DATE H.HASEGAWA 1994/10/26	TITLE NEW INTERNATIONAL CONN. HEADER AND ASSY		MATERIAL NO. SEE CHART DOCUMENT NO. SD-5219-02A*-* SHEET NO. 1 OF 1
	▽=0	4 PLACES ± --- ± ---	CHECKED BY DATE H.HIRAMOTO 1996/02/26			
	▽=0	3 PLACES ± --- ± ---	APPROVED BY DATE M.FUKUSHIMA 1996/02/26			
	▽=0	2 PLACES ± 0.25 ± ---				
▽=0	1 PLACE ± 0.35 ± ---					
		0 PLACE ± ±				
		ANGULAR ± 1°				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		