

U St Rohs M

# LF SERIES CLASS CC/CD AND MIDGET (10x38) FUSE BLOCKS

# 600 V



# **Description**

The Littelfuse Class CC, CD and midget blocks offer generous space savings and enhanced value. DIN-rail mounting and universal mounting holes are available as well as an indication feature on all Class CD fuse blocks.

### **Features/Benefits**

- Space-saving design
- Universal mounting holes for easy replacement
- Indication offered on CD blocks
- One hand release from DIN rail optional
- Rejection feature that prevents the insertion of fuses with lower interrupting rating or voltage ratings
- Clip design reduces resistance and heat
- Non DIN-rail fuse blocks have interlocking feature allowing ganging for any number of poles
- Covers available for all amperages to enhance safety

# **Specifications**

Voltage Rating Ampere Ratings	600 Vac/dc L600M Midget (10x38): 30 A L600C Class CC: 30 A LFC Class CD: 60 A L600CM Class CC & Midget: 30 A							
<b>Dielectric strength</b>	1200 V minimum							
Materials	Clip/terminals: Tin-plated copper alloy Box lug: Copper Screw & captive pressure plate: Zinc-plated stee Base: Thermoplastic UL94 V-0 flammability rating							
Withstand Rating	L60030C: 200kA							
(SCCR)	L60030M:10kA, 20kA or 100kA based on the Midget fuse used							
	LFC600: 200kA							
Approvals	L600M: UL Recognized (File: E14721) CSA Certified (File: LR7316)							
	L600C: UL Listed (File: E14721) CSA Certified (File: LR7316)							
	LFC: UL Listed (File: E14721) CSA Certified (File: LR7316)							
	L600CM: UL Recognized (File: E14721) CSA Certified (File: LR7316)							
Environmental	RoHS Compliant, Lead (Pb) Free							

### **Recommended Fuses**

Class CC Blocks:	CCMR, KLDR, KLKR
Class CM Block:	Fuses same as CC & Midget Blocks
Class CD Blocks:	CCMR
Midget Blocks:	BLF, BLN, BLS, FLA, FLM, FLQ,
	FLU, KLK, KLKD, KLQ

### **Web Resources**

Sample requests and technical downloads: littelfuse.com/fuseblocks

# Ordering Information (L600C Class CC and L600M Midget 30 A)

ING NG	ES	CLASS CC ORDERING NUMBER		MIDGET ORDERING NUMBER		CONNECTOR	TOPOUL	WIRE			BASE	COVER
AMP RATING	POL	NON-DIN*	DINR	NON-DIN*	DINR	TYPE	TORQUE	RANGE	WIRE TYPE		TEMP	ORDERING NUMBER <sup>†</sup>
	1	L60030C1C	L60030C1CDINR	L60030M1C	L60030M1CDINR		4.0 N-m (35 in-lbs)	6-14 AWG	CU	Solid / Stranded		
30	2	L60030C2C	L60030C2CDINR	L60030M2C	L60030M2CDINR	Box Lug					125°C	SPL001
	3	L60030C3C	L60030C3CDINR	L60030M3C	L60030M3CDINR							
	1	L60030C1PQ	L60030C1PQDINR	L60030M1PQ	L60030M1PQDINR	Pressure Plate	2.3 N-m (20 in-lbs)	10-14 AWG			125°C	SPL001
30	2	L60030C2PQ	L60030C2PQDINR	L60030M2PQ	L60030M2PQDINR	w/Q.C. Terminal						
	3	L60030C3PQ	L60030C3PQDINR	L60030M3PQ	L60030M3PQDINR							
	1	L60030C1SQ	L60030C1SQDINR	L60030M1SQ	L60030M1SQDINR	Sorow	2.3 N-m (20 in-lbs)	10-14 AWG				
30	2	L60030C2SQ	L60030C2SQDINR	L60030M2SQ	L60030M2SQDINR	Screw w/Q.C. Terminal					125°C	SPL001
	3	L60030C3SQ	L60030C3SQDINR	L60030M3SQ	L60030M3SQDINR							

### Ordering Information (L600CM Class CC and Midget Combination 30 A)

<b>MP</b> MING	POLES		COMBINATION 2 CLASS CC / 1 MIDGET ORDERING NUMBER		CONNECTOR	TORQUE	WIRE	WIRE TYPE	BASE	COVER ORDERING NUMBER <sup>†</sup>
BAA	CLASS CC	CC MIDGET NON-DIN DINR		TYPE		RANGE		TEMP		
30	2	1	L60030CM3PQ	_	Pressure Plate w/Q.C. Terminal	2.3 N-m (20 in-lbs)	10-14 AWG	CU Only Solid / Stranded	125°C	SPL001



# LF SERIES CLASS CC/CD AND MIDGET (10X38) FUSE BLOCKS


# **Ordering Information (LFC Class CD 60 A)**

	amp Rating	POLES	ORDERING NUMBER	CONNECTOR TYPE	TORQUE	WIRE RANGE	WIRE TYPE		BASE TEMP RATING	DIN RAIL MOUNT	INDICATION	COVER ORDERING NUMBER <sup>†</sup>
		1	LFC600601CID		5.6 N-m (50 in-lbs)	2-4 AWG		Solid /				
	60	2	LFC600602CID	Box Lug			CU-AL	Stranded	125°C	•	•	LFC60060FBC
	3	LFC600603CID		2.8 N-m (25 in-lbs)	6-14 AWG		Stranded					


\* Gangable – <sup>+</sup> Covers sold individually. One cover needed for each pole.


### **Dimensions mm (inches)**


### L600M-DINR Midget and L600C-DINR Class CC 30 A




#### L600M Midget, L600C Class CC and L600CM Combination 30 A











# LF SERIES CLASS CC/CD AND MIDGET (10X38) FUSE BLOCKS

# **Dimensions mm (inches)**

#### LFC CLASS CD 60 A

