



规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC:100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50-60Hz) 60S min.
操作力 Operation force	≦ 180±30gf ≦ 300±50gf
寿命试验 Operating Life	50,000 cycles 30,000 cycles
行程 Travels	0.25±0.1mm



RECOMMENDED P.C.B. LAYOUT

安装尺寸图

PRODUCT NO.: 1TS002*****-CT

- 轻触开关
- 3X6系列
- 外形:
- A=插脚
- B=贴片
- C=贴片带柱
- D=贴片2.5高
- E=贴片带柱8.8
- F=贴片10.2
- 按钮颜色:
- 底座颜色:
- 盖板颜色:
- 操作力度:
- 手感:
- 产品高度(H):
- 材料:
- 非编带
- 编带, 不启用

初始颜色
则不启用

130=130±20gf
160=160±30gf
180=180±30gf
220=220±40gf
250=250±50gf
300=300±50gf

0=常规
1=大手感
2=小手感
3=特殊手感

430=4.3mm
500=5.0mm

0=PA66
1=LCP+PPA
2=LCP
3=PA66+PPA
4=新增材质
依次增加

5 ACTUATOR

6 COVER

7 DOME

8 HOUSING

9 TERMINAL

10 PART NAME

11 QUANTITY

12 MATERIAL

13 FINISH

14 NAME(INTENDED USE)

15 TACT SWITCH

16 PART NO.(INTENDED USE)

17 TITLE:

18 PRODUCT DRAWING

19 APPD: ZO 2015/11/12

20 DWG NO.: 1TS002C

21 CHKD: M.H.LI 2015/11/12

22 DR: WP.LU 2015/11/11

23 HON YUAN

24 HON YUAN PRECISION IND. CO.,LTD.

25 SHENZHEN, CHINA.

26 SCALE SHEET

27 10/1

28 2/4

29 REV.

30 D

31 THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.