




CIRCUIT DIAGRAM  
回路图



RECOMMENDED P.C.B. LAYOUT  
安装尺寸图



REV	ECN NO.	APPD
A	HC110006	PRIOJOM
B	HC120062	PRIOJOM
C	HC130004	PRIOJOM
D	HC140000	PRIOJOM

规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC:100V/ 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V/50-60HZ) 60S min.
操作力 Operation force	≤ 180±30gf      ≤ 300±50gf
寿命试验 Operating Life	50,000 cycles      30,000 cycles
行程 Travels	0.25±0.1mm

PRODUCT NO.: 1TS002E\*\*\*\*\*

- 轻触开关 3X6系列
- 外形: A=插脚, B=贴片, C=贴片带柱, K=贴片带柱8.8, L=贴片10.2
- 按钮颜色: 底座颜色: 盖板颜色:
- 操作力度: 0=常规(弹片), 1=大手感(弹片), 2=小手感(弹片), 3=特殊手感(弹片)
- 产品高度(H): 250=2.5mm
- 其它: 有无贴膜: 0=不贴膜, 1=贴膜; CT=编带(非编带, 不启用)

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	ACTUATOR	1	LCP	RED
4	COVER	1	STAINLESS STEEL	NATURAL
3	DOME	1	STAINLESS STEEL	Ag-PLATED
2	HOUSING	1	LCP	BLACK
1	TERMINAL	1	BRASS	Ag-PLATED

NAME (INTENDED USE)	HON YUAN
3X6 T/H SERIES TACT SWITCH	HON YUAN PRECISION IND. CO., LTD. SHENZHEN, CHINA.
PART NO. (INTENDED USE)	PRODUCT DRAWING
ITSO02E*****	
APPD: ZO 8/08/2014	DWG NO.: 1TS002E
CHKD: M.H.LI 8/08/2014	
DR: WP.LU 8/07/2014	

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.

SCALE	SHEET	REV.
10/1	2/2	D