


规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC:100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	160±30gf / 250±50gf
寿命试验 Operating Life	100,000 cycles / 70,000 cycles
行程 Travels	0.25±0.1mm

RECOMMENDED P.C.B. LAYOUT

安装尺寸图



PRODUCT NO.: 1TS005A****-***** - CT

- 轻触开关
- 系列
- 外形:
- 按钮颜色:
- 底座颜色:
- 盖板颜色:
- 初始颜色, 则不启用
- 操作力度:
- 手感:
- 材质:
- 0=初始材质
- 1=新增材质
- 依次增加
- 产品高度(H):
- 430=4.3mm
- 700=7.0mm
- 编织带
- 非编织带, 不启用

5	COVER	1	Stainless Steel	NATURAL
4	ACTUATOR	1	PPA	BLACK
3	DOVE	1	Phosphor Bronze/Ag	Ag-PLATED
2	TERMINAL	1	BRASS	Ag-PLATED
1	HOUSING	1	PPA	BLACK
ITEM	PART NAME	QUANTITY	MATERIAL	FINISH

X. ± 0.3	X. ± 3'	UNITS	MM
X. ± 0.2	X. ± 2'	MAT'L	
.XX ± 0.1	.XX' ± 1'	FINISH	
.XXX ± 0.05	.XXX' ± 0.5'		
NAME(INTENDED USE)		HON YUAN	
TACT SWITCH		HON YUAN PRECISION IND. CO.,LTD.	
PART NO.(INTENDED USE)		SHENZHEN, CHINA.	
1TS005A-****-***1		TITLE:	
		PRODUCT DRAWING	
APPD: ZO 2013/06/29		DWG NO.:	
		1TS005A	
CHKD: M.H.LI 2013/06/29		SCALE	
DR.Y.Y.Chen 2013/06/29		10/1	
		SHEET	
		2/2	
		REV.	
		A	

THESE DIMENSIONS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.