


规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	≤180±30gf    ≥250±50gf
寿命试验 Operating life	100,000cycles    100,000cycles
行程 Travels	看左侧编码说明



PRODUCT NO. : 1 T S 0 0 9 \*\*\*\*\* - C T

- 轻触开关  
TMRV系列
- 外形: A=弧盖弯脚 B=平盖弯脚 C=弧盖平脚 D=平盖平脚
- 按钮颜色: 盖座颜色: 盖板颜色: 初始颜色 则不启用
- 操作力度: 160=160±30gf 180=180±30gf 250=250±50gf 260=260±50gf 280=280±50gf 300=300±50gf
- 手感: 0=常规 1=大手感 2=小手感 3=特殊手感
- 产品高度(H): 430=4.3mm (行程: 0.7±0.2mm) 500=5.0mm (行程: 1.3±0.2mm)
- 材质: 0=LCP 1=新增材质 依次增加
- 非编带, 不启用

5	COVER	1	LCP	BLACK
4	ACTUATOR	1	SILICONE	/
3	CONTACT	1	STAINLESS STEEL	Ag-PLATED
2	TERMINAL	2	BRASS	Ag-PLATED
1	HOUSING	1	LCP	BLACK
ITEM	PART NAME	QUANTITY	MATERIAL	FINISH

X. ± 0.3	X' ± 3'	UNITS	MM
X ± 0.2	X' ± 2'	MAT'L	
.XX ± 0.1	.XX' ± 1'	FINISH	
.XXX ± 0.05	.XXX' ± 0.5'	Q'TY	
NAME/(INTENDED USE) TMRV SERIES TACT SWITCH			
PART NO.(/INTENDED USE) 1TS009C-****-****0			
APPD: ZO 2015-11-10			
CHGD: M.H.LI 2015-11-10			
DR: Y.Y.Chen 2015-11-10			
DWG NO.: 1TS009C			
TITLE: PRODUCT DRAWING			
HON YUAN HON YUAN PRECISION IND. CO.,LTD. SHENZHEN, CHINA.			
SCALE SHEET REV.			
10/1 1/1 B			

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO.,LTD. ANY REPRODUCTION OR USE IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.