



PRODUCT NO.: 1TS009C\*\*\*\*\*-CT

- 轻触开关  
TMRV系列
- 外形:  
A=弧盖弯脚  
B=平盖弯脚  
C=弧盖平脚  
D=平盖平脚
- 按钮颜色:  
底座颜色:  
盖板颜色:
- 操作力度:  
160=160±30gf  
180=180±30gf  
250=250±50gf  
260=260±50gf  
280=280±50gf  
300=300±50gf
- 手感:  
0=常规  
1=大手感  
2=小手感  
3=特殊手感
- 材质:  
0=LCP  
1=新增材质  
依次增加
- 产品高度(H):  
430=4.3mm (行程: 0.7±0.2mm)  
500=5.0mm (行程: 1.3±0.2mm)
- 非编带, 不启用

规格 Specifications

额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	≤180±30gf ≥250±50gf
寿命试验 Operating life	100,000cycles / 100,000cycles
行程 Travels	看左侧编码说明

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	COVER	1	LCP	BLACK
4	ACTUATOR	1	SILICONE	/
3	CONTACT	1	STAINLESS STEEL	Ag-PLATED
2	TERMINAL	2	BRASS	Ag-PLATED
1	HOUSING	1	LCP	BLACK

UNITS	MM	NAME/(INTENDED USE)	HON YUAN
MAT'L		TMRV SERIES TACT SWITCH	HON YUAN PRECISION IND. CO.,LTD. SHENZHEN, CHINA.
FINISH		1TS009C-****-****0	PRODUCT DRAWING
Q'TY		APPD: ZO 2015-11-10	DWG NO.: 1TS009C
		CHKD: M.H.LI 2015-11-10	SCALE SHEET
		DR: Y.Y.Chen 2015-11-10	10/1
			1/1
			REV. B

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO.,LTD. ANY REPRODUCTION OR USE IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.