



P/N LEGEND

	A1252	H-XP	XXX
	①	②	③ ④
① Series No.			
② Connector type: H=Housing			
③ No. of circuits			
④ Option code:			
	Blank=Color:Gray(7529C~7530C)		
	BK=Color:Black		
	BE=Color:Beige		
	BL=Color:Blue(285C)		

SPECIFICATIONS

Current Rating: 1A AC,DC  
 Voltage Rating: 150V AC,DC  
 Temperature Range: -25°C ~ +85°C  
 Contact Resistance: 30mΩ Max.  
 Insulation Resistance: 500MΩ Min.  
 Withstanding Voltage: 500V AC/minute  
 Material: Nylon 66,UL94V-0

Circuit No.	Dimensions	
	A	B
02P	1.25	4.15
03P	2.50	5.40
04P	3.75	6.65
05P	5.00	7.90
06P	6.25	9.15
07P	7.50	10.40
08P	8.75	11.65
09P	10.00	12.90
10P	11.25	14.15
11P	12.50	15.40
12P	13.75	16.65
13P	15.00	17.90
14P	16.25	19.15
15P	17.50	20.40

				燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.		
		UNIT	SCALE	SHEET	TITLE:	
		mm	1 : 1	1 of 1	1.25mm PITCH SINGLE ROW HOUSING	
		DRAWN BY	APPROVED BY			
		董正一	董正一			
		2001.02.01	2001.02.01		DRAW NO. :	
		GENERAL TOLERANCE			A1252H-XP	
B3	EN1204230116	2012.04.23	陳錦展	X.X±0.25	REV. B3	
B2	EN1104200112	2011.04.20	陳錦展	X.XX±0.15		
REV.	DESCRIPTION	DATE	NAME	X.XXX±0.05		