



P/N LEGEND

A1252 H-2XNP XXX			
①	②	③	④
① Series No.	② Connector type: H=Housing	③ No. of circuits	④ Option code:
Blank=Color:Gray(7529C~7530C)			
BL=Color:Blue(285C)			
BK=Color:Black			

SPECIFICATIONS

Current Rating: 1A AC,DC
 Voltage Rating: 150V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 30mΩ Max.
 Insulation Resistance: 500MΩ Min.
 Withstanding Voltage: 500V AC/minute
 Material: Nylon 66,UL94V-0

Circuit No.	Dimensions			
	A	B	C	D
2X05P	5.00	10.40	8.00	9.00
2X06P	6.25	11.65	9.25	10.25
2X07P	7.50	12.90	10.50	11.50
2X10P	11.25	16.65	14.25	15.25
2X15P	17.50	22.90	20.50	21.50
2X17P	20.00	25.40	23.00	24.00
2X18P	21.25	26.65	24.25	25.25
2X20P	23.75	29.15	26.75	27.75
2X21P	25.00	30.40	28.00	29.00
2X25P	30.00	35.40	33.00	34.00

 燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.			
UNIT	SCALE	SHEET	TITLE:
mm	1 : 1	1 of 1	1.25mm PITCH DUAL ROW HOUSING
DRAWN BY	APPROVED BY		
董正一	董正一		
2001.02.01	2001.02.01		
B5	EN1301040007	2013.01.04	陳錦展
B4	EN1109300443	2011.11.07	陳錦展
B3	EN1104200112	2011.04.20	陳錦展
REV.	DESCRIPTION	DATE	NAME
GENERAL TOLERANCE			
	X. X±0.25	ANGLE±	
	X. XX±0.15		
	X. XXX±0.05		
DRAW NO. :			REV.
A1252H-2XNP			B5