



P/N LEGEND

A1252 WR-S-XP XXX				
①	②	③	④	⑤
① Series No.	② Connector type: WR=Right angle	③ Mounting type: S=SMT	④ No. of circuits	⑤ Option code:
D01=Contacts/Gold-flash and Solder tabs/Gold-flash				

SPECIFICATIONS

Current Rating: 1A AC,DC
 Voltage Rating: 150V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 30mΩ Max.
 Insulation Resistance: 500MΩ Min.
 Withstanding Voltage: 500V AC/minute
 Pin Material: Brass/Gold-flash
 Solder Tabs: Phosphor Bronze/Gold-flash
 Material: Nylon 6T,UL94V-0
 Color: Natural(Beige)

Circuit No.	Dimensions		
	A	B	C
02P	1.25	4.15	6.25
03P	2.50	5.40	7.50
04P	3.75	6.65	8.75
05P	5.00	7.90	10.00
06P	6.25	9.15	11.25
07P	7.50	10.40	12.50
08P	8.75	11.65	13.75
09P	10.00	12.90	15.00
10P	11.25	14.15	16.25
11P	12.50	15.40	17.50
12P	13.75	16.65	18.75
13P	15.00	17.90	20.00
14P	16.25	19.15	21.25
15P	17.50	20.40	22.50

 燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.				UNIT	SCALE	SHEET	TITLE:
				mm	1 : 1	1 of 2	1.25mm PITCH 90° SINGLE ROW WAFER- SMT TYPE, W/O BOSS
DRAWN BY		APPROVED BY					
歐陽小強		董正一					
2007.01.05		2007.01.05					
GENERAL TOLERANCE							
				X. X±0.25	ANGLE±		
				X. XX±0.15			
				X. XXX±0.05			
A1	EN1202060018	2012.02.06	陳錦展				
REV.	DESCRIPTION	DATE	NAME				
				DRAW NO.:		REV.:	
				A1252WR-S-XP		A1	