



SPECIFICATIONS
 Current Rating: 2A AC,DC
 Voltage Rating: 250V AC,DC
 Temperature Range: -25°C ~ +85°C
 Contact Resistance: 30mΩ Max.
 Insulation Resistance: 1000MΩ Min.
 Withstanding Voltage: 800V AC/minute
 Pin Material: Brass/Tin-plated
 Material: Nylon 66,UL94V-0
 Color: Black

Ordering Information & Dimensions

PART NO.	Dimensions	
	A	B
A2211WR-2X02P	2.00	6.00
A2211WR-2X03P	4.00	8.00
A2211WR-2X04P	6.00	10.00
A2211WR-2X05P	8.00	12.00
A2211WR-2X06P	10.00	14.00
A2211WR-2X07P	12.00	16.00
A2211WR-2X08P	14.00	18.00
A2211WR-2X09P	16.00	20.00
A2211WR-2X10P	18.00	22.00
A2211WR-2X11P	20.00	24.00
A2211WR-2X12P	22.00	26.00
A2211WR-2X13P	24.00	28.00
A2211WR-2X14P	26.00	30.00
A2211WR-2X15P	28.00	32.00
A2211WR-2X16P	30.00	34.00
A2211WR-2X17P	32.00	36.00
A2211WR-2X18P	34.00	38.00
A2211WR-2X19P	36.00	40.00
A2211WR-2X20P	38.00	42.00



				UNIT		SCALE	SHEET	TITLE:
				mm			1 of 1	2.00mm PITCH 90° WAFER
DRAWN BY		APPROVED BY		GENERAL TOLERANCE X. X±0.25 ANGLE± X. XX±0.15 X. XXX±0.05				
董正一		董正一						
2001.02.01		2001.02.01		DRAW NO.:				
REVISE		NEW RELEASE		A2211WR-2XNP				
2007.02.27		2005.12.05		REV. B1				
REV.	DESCRIPTION	DATE	TOLERANCE					