



### SPECIFICATIONS

Current Rating: 2A AC,DC  
 Voltage Rating: 250V AC,DC  
 Temperature Range: -25°C ~ +85°C  
 Contact Resistance: 30mΩ Max.  
 Insulation Resistance: 1000MΩ Min.  
 Withstanding Voltage: 800V AC/minute  
 Pin Material: Brass/Gold-flash  
 Material: Nylon 6T,UL94V-0  
 Cap: Nylon 6T,UL94V-0,Natural(Beige)  
 Color: Natural(Beige)

### Ordering Information & Dimensions

PART NO.	Dimensions		
	A	B	C
A2211WVA-SF-2X02P	2.00	6.00	4.00
A2211WVA-SF-2X03P	4.00	8.00	6.00
A2211WVA-SF-2X04P	6.00	10.00	8.00
A2211WVA-SF-2X05P	8.00	12.00	10.00
A2211WVA-SF-2X06P	10.00	14.00	12.00
A2211WVA-SF-2X07P	12.00	16.00	14.00
A2211WVA-SF-2X08P	14.00	18.00	16.00
A2211WVA-SF-2X09P	16.00	20.00	18.00
A2211WVA-SF-2X10P	18.00	22.00	20.00
A2211WVA-SF-2X11P	20.00	24.00	22.00
A2211WVA-SF-2X12P	22.00	26.00	24.00
A2211WVA-SF-2X13P	24.00	28.00	26.00
A2211WVA-SF-2X14P	26.00	30.00	28.00
A2211WVA-SF-2X15P	28.00	32.00	30.00
A2211WVA-SF-2X16P	30.00	34.00	32.00
A2211WVA-SF-2X17P	32.00	36.00	34.00
A2211WVA-SF-2X18P	34.00	38.00	36.00
A2211WVA-SF-2X19P	36.00	40.00	38.00
A2211WVA-SF-2X20P	38.00	42.00	40.00

				JOINT TECH ELECTRONIC IND. CO., LTD. JOY DAY INDUSTRIAL CO., LTD.		
		UNIT	SCALE	SHEET		
		mm		1 of 2		
		DRAWN BY		APPROVED BY		
		伍建永		謝瑞清		
		2005.11.04		2005.11.04		
		GENERAL TOLERANCE				
B3	REVISE	2008.02.19				
B2	REVISE	2007.02.27				
B1	REVISE	2006.03.27	X.X ± 0.25	ANGLE ±		
B0	NEW RELEASE	2005.12.05	X.XX ± 0.15			
REV.	DESCRIPTION	DATE	X.XXX ± 0.05			
		TITLE:			2.00mm PITCH 180 °WAFER-SMT TYPE	
		DRAW NO.:			REV.:	
		A2211WVA-SF-2XNP			B3	