



P. C. B Layout

一. 电气性能:

- 1-1. 额定电流: 3A AC DC.
- 1-2. 接触电阻:  $\leq 20m\Omega$
- 1-3. 绝缘电阻:  $\geq 1000M\Omega$
- 1-4. 耐压: 550V AC/Minute

二. 物理特性:

- 2-1. 操作温度:  $-55^{\circ}C \sim 105^{\circ}C$
- 2-2. 焊接温度:  $+260^{\circ}C$ , 10s max

三. 材质:

- 3-1. 塑胶: PA6T (Black) UL94V-0
- 3-2. 插针: Brass/Gold plated

PIN	A	B	C
4	5.08	3.81	2.51
5	6.35	5.08	3.81
6	7.62	6.35	5.08
7	8.89	7.62	6.35
8	10.16	8.89	7.62
9	11.43	10.16	8.89
10	12.70	11.43	10.16
11	13.97	12.70	11.43
12	15.24	13.97	12.70
13	16.51	15.24	13.97
14	17.78	16.51	15.24
15	19.05	17.78	16.51
16	20.32	19.05	17.78
17	21.59	20.32	19.05
18	22.86	21.59	20.32
19	24.13	22.86	21.59
20	25.40	24.13	22.86
21	26.67	25.40	24.13
22	27.94	26.67	25.40
23	29.21	27.94	26.67
24	30.48	29.21	27.94
25	31.75	30.48	29.21
26	33.02	31.75	30.48
27	34.29	33.02	31.75
28	35.56	34.29	33.02
29	36.83	35.56	34.29
30	38.10	36.83	35.56
31	39.37	38.10	36.83
32	40.64	39.37	38.10
33	41.91	40.64	39.37
34	43.18	41.91	40.64
35	44.45	43.18	41.91
36	45.72	44.45	43.18
37	46.99	45.72	44.45
38	48.26	46.99	45.72
39	49.53	48.26	46.99
40	50.80	49.53	48.26
41	52.07	50.80	49.53
42	53.34	52.07	50.80
43	54.61	53.34	52.07
44	55.88	54.61	53.34
45	57.15	55.88	54.61
46	58.42	57.15	55.88
47	59.69	58.42	57.15
48	60.96	59.69	58.42
49	62.23	60.96	59.69
50	63.50	62.23	60.96

深圳市威电康精密科技有限公司

图名:	P21.27-LT-2xNAT-2.0MM		
	图号:	XXXXXXXXXXXXXXXXXXXXXX	
未标注公差			
XX.	±0.40	XX.°	±2°
X.	±0.30	.XX°	±1°
.X	±0.20		
.XX	±0.15		
绘制:	韩金锋	单位:	MM
签发:		比例:	1:1
审核:		视图:	