


SWITCH CONNECTOR



	MATERIAL	PLATING
center pin	brass	tin
terminal 1	brass	tin
terminal 2	copper alloy	tin
terminal 3	brass	tin
plastic	PA66	

REVISIONS					UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION	
ΔX					ANGULAR	±5°	DSND		DATE	SCALE: N/A	MODEL TYPE: DC POWER JACK		
ΔX					L ≤ 4	±0.2	DWN		DATE	VIEW:	PART NO.:		
ΔX					4 < L ≤ 16	±0.3	CHKD		DATE	UNIT: mm	DWG NO.:		
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4	APPD		DATE	SIZE: A4	DC-022-5A-2.5		
					L > 63	±0.5					1.0g	1/1	A0