

● ELECTRICAL PARAMETERS

谐振器产品技术指标	Min	Max	Units
1. Holder Type(型号规格)	SEAM 3.2*2.5		
2. Mode of Oscillation (振动模式)	Fundamental		
3. Frequency (标称频率)	12.288000		MHz
4. Load Capacitance (CL) (负载电容)	12		pF
5. Drive Level (激励功率)	100		uw
6. Equivalent Resistance (谐振电阻)		60	Ω
7. Shunt Capacitance (Co) (静态电容)	0	5	pF
8. Motional Capacitance (C1) (动态电容)	N/A		fF
9. Frequency Tolerance at 25°C (调整频差)	-10	10	ppm
10. Stability over operation temperature (温度频差)	± 20		ppm
11. Insulation Resistance (at DC 100V) (绝缘电阻)	500		MΩ
12. Operating Temperature Range (工作温度范围)	-40	85	°C
13. Storage Temperature Range (储存温度范围)	-40	85	°C
14. Aging (老化率)	± 5		ppm/year
15. DLD2	N/A	N/A	Ω
16. FLD2		N/A	ppm
17. RLD2		N/A	Ω
18. SPDB		N/A	db
19. Other(其它)	N/A		

OUTLINE DIMENSIONS(UNIT:mm) 外形尺寸 (单位: mm)

