




SPECIFICATIONS

Current rating: 3A AC/DC
 Voltage rating: 250V AC/DC
 Contact resistance: 20mΩ max.
 Withstand voltage: 1000V AC/min
 Insulation resistance: 1000MΩ/min.
 Temperature range: -25°C~+85°C
 Applicable PC board thickness: 0.063"(1.6)

Material:

Part No: 2-20
 HOUSING: Nylon66, UL 94V-2



Poles	Part No.	Dimension mm		
		A	B	C
2	2501HB-2P	2.50	5.70	7.20
3	2501HB-3P	5.00	8.20	9.70
4	2501HB-4P	7.50	10.70	12.20
5	2501HB-5P	10.00	13.20	14.70
6	2501HB-6P	12.50	15.70	17.20
7	2501HB-7P	15.00	18.20	19.70
8	2501HB-8P	17.50	20.70	22.20
9	2501HB-9P	20.00	23.20	24.70
10	2501HB-10P	22.50	25.70	27.20
11	2501HB-11P	25.00	28.20	29.70
12	2501HB-12P	27.50	30.70	32.20
13	2501HB-13P	30.00	33.20	34.70
14	2501HB-14P	32.50	35.70	37.20
15	2501HB-15P	35.00	38.20	39.70
16	2501HB-16P	37.50	40.70	42.20
17	2501HB-17P	40.00	43.20	44.70
18	2501HB-18P	42.50	45.70	47.20
19	2501HB-19P	45.00	48.20	49.70
20	2501HB-20P	47.50	50.70	52.20

TOLERANCE TABLE

.0	±0.20
.00	±0.10
.000	±0.05

APPROVED: DATE: **CHANGED:** DATE: **DRAM:** LYF

2008-04-07

TITLE: 2501HB-XP (带扣)

CLIENT P/N /
 UNIT mm SCALE free
 FILE NO. Chantw-2501-0005 REV. A

深圳市如科盟实业有限公司
 CHANKLEMENT INDUSTRYCO., LTD