


RECOMMENDED P.C.B LAYOUT



Specification
 Insulator Material: Polyesetr, UL94V-0
 Standard:P.B.T
 Contact plated: Gold Over Nickel
 Poles:2~40P
 Current Rating : 3Amp
 Contact Resistance:20 Milliohms Max
 Insulation Resistance : 1000MΩ Min.
 Dielectric withstanding Voltage:AC 500V
 Operation Temperature : -40℃ -- +105℃

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	TITLE:			
CHECKED:	DATE:	210RE-1*XP (6.0/4.8/2.54/3.0)			
DRAWN:	DATE:	CLIENT P/N	SCALE	free	REV.
LXF	2008-04-29	/	mm	free	A
		UNIT	SCALE	free	REV.
		FILE NO.	Clkmtw-210-00004		A

深圳市灿科盟实业有限公司
 CHANKEMENG INDUSTRYCO., LTD