


PART NO.	NO.OF POS.	DIM.A	DIM.B	Projection (P)	Short (S)
DSIC01LS	1	3.48		DSIC01LS-P	DSIC01LS-S
DSIC02LS	2	6.02	2.54	DSIC02LS-P	DSIC02LS-S
DSIC03LS	3	8.56	5.08	DSIC03LS-P	DSIC03LS-S
DSIC04LS	4	11.10	7.62	DSIC04LS-P	DSIC04LS-S
DSIC05LS	5	13.64	10.16	DSIC05LS-P	DSIC05LS-S
DSIC06LS	6	16.18	12.70	DSIC06LS-P	DSIC06LS-S
DSIC07LS	7	18.72	15.24	DSIC07LS-P	DSIC07LS-S
DSIC08LS	8	21.26	17.78	DSIC08LS-P	DSIC08LS-S
DSIC09LS	9	23.80	20.32	DSIC09LS-P	DSIC09LS-S
DSIC10LS	10	26.34	22.86	DSIC10LS-P	DSIC10LS-S
DSIC12LS	12	31.42	27.94	DSIC12LS-P	DSIC12LS-S

XKLB SWITCH CONNECTOR

CIRCUIT



SPECIFICATION

Contact Rating	25mA 24V DC
Contact Resistance	100mΩ max.
Insulation Resistance	100MΩ min. 500V DC
Dielectric Strength	500V AC/1 minute
Operating Force	1 000gf max.
Travel	1mm
Operating Life	2 000 cycles
Operating Temp.	-20 C +85 C
Storage Temp.	-40 C +85 C

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	DSND	DATE	SCALE: N/A	MODEL TYPE: DIP SWITCH
ΔX					ANGLAR ±5°	DWN	DATE	VIEW:	PART NO.:
ΔX					L ≤ 4 ±0.2	CHKD	DATE	UNIT: mm	DWG NO.: DSICXXLS-X
ΔX					4 < L ≤ 16 ±0.3	APPD	DATE	SIZE: A4	
					16 < L ≤ 63 ±0.4	XKB INDUSTRIAL PRECISION CO., LIMITED			
					L > 63 ±0.5				