



PART NO.	NO.OF POS.	DIM.A	DIM.B	Projection (P)	Short (S)
DSIC01LH	1	2.44		DSIC01LH-P	DSIC01LH-S
DSIC02LH	2	4.98	2.54	DSIC02LH-P	DSIC02LH-S
DSIC03LH	3	7.52	5.08	DSIC03LH-P	DSIC03LH-S
DSIC04LH	4	10.06	7.62	DSIC04LH-P	DSIC04LH-S
DSIC05LH	5	12.60	10.16	DSIC05LH-P	DSIC05LH-S
DSIC06LH	6	15.14	12.70	DSIC06LH-P	DSIC06LH-S
DSIC07LH	7	17.68	15.24	DSIC07LH-P	DSIC07LH-S
DSIC08LH	8	20.22	17.78	DSIC08LH-P	DSIC08LH-S
DSIC09LH	9	22.76	20.32	DSIC09LH-P	DSIC09LH-S
DSIC10LH	10	25.30	22.86	DSIC10LH-P	DSIC10LH-S
DSIC12LH	12	30.38	27.94	DSIC12LH-P	DSIC12LH-S




**CIRCUIT**



**SPECIFICATION**

- Contact Rating 25mA, 24V DC
- Contact Resistance 100mΩ max.
- Insulation Resistance 100MΩ min. 500V DC
- Dielectric Strength 500V AC/1 minute
- Operating Force 1,000gf max.
- Travel 1mm
- Operating Life 2,000 cycles
- Operating Temp. -20°C ~ +85°C
- Storage Temp. -40°C ~ +85°C



					DSND		DATE		SCALE: N/A	MODEL TYPE: DIP SWITCH		
ΔX					DWN		DATE		VIEW:	PART NO.:		
ΔX					CHKD		DATE		UNIT: mm	DWG NO.: DSICXXLH-X		
ΔX					APPD		DATE		SIZE: A4			
MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES					WEIGHT	SHEET	REVISION
					XKB INDUSTRIAL PRECISION CO., LIMITED					1.0g	1/1	A0
REVISIONS												
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn												