






Pin数	尺寸A	尺寸B	尺寸C
2x3	5.08	12.94	15.24
2x4	7.62	15.48	17.78
2x5	10.16	18.02	20.32
2x6	12.70	20.56	22.86
2x7	15.24	23.10	25.40
2x8	17.78	25.64	27.94
2x9	20.32	28.18	30.48
2x10	22.86	30.72	33.02
2x11	25.40	33.26	35.56
2x12	27.94	35.80	38.10
2x13	30.48	38.34	40.64
2x14	33.02	40.88	43.18
2x15	35.56	43.42	45.72
2x16	38.10	45.96	48.26
2x17	40.64	48.50	50.80
2x18	43.18	51.04	53.34
2x19	45.72	53.58	55.88
2x20	48.26	56.12	58.42
2x21	50.80	58.66	60.96
2x22	53.34	61.20	63.50
2x23	55.88	63.74	66.04
2x24	58.42	66.28	68.58
2x25	60.96	68.82	71.12
2x26	63.50	71.36	73.66
2x27	66.04	73.90	76.20
2x28	68.58	76.44	78.74
2x29	71.12	78.98	81.28
2x30	73.66	81.52	83.82
2x31	76.20	84.06	86.36
2x32	78.74	86.60	88.90



技术规范:
 额定电流 : 3AMP
 适用温度 : -40°Cto+105°C
 接触电阻 : 20mΩ Max
 绝缘电阻 : 1000MΩ Min
 耐电压 : AC1000V
 绝缘材料 : Polyester (UL94V-0)
 Standard:PBT
 端子材质 : Brass
 电镀规范 : Au or Sn Over 50u" Ni

B		3-88		XX-A-A-R-XX-X-0					
筒牛系列	间距 1-1.27mm 2-2.0mm 3-2.54mm	塑高 5.65-565 5.7-57 6.35-64 7.1-71(塑) 1.27 间距2.54 9.0-90 13.1-131	PIN位 6~64P	电镀 A-1u" B-2u" C-5u" D-15u" E-镀锡 F-半金锡	材质 A-PBT B-PA46 C-PAGT D-PAGT E-LCP	角度 S=180° R=90° M=SMT Y=刺破压线	缺PIN K-20=20	颜色 B=Black G=Grey Y=Yellow W=White R=Red U=Blue	流水号 0=常用规格 1= 2=

变更单号	变更标记	变更日期	描述	变更人	审核	批准	未标公差	比例	1:1	单位	mm	页数	1 OF 1	AO	
							角度	±2°							
							X.	±0.25	设计		日期				2.54间距筒牛, 90°, 塑高8.8mm
							.X	±0.15	审核		日期				Spec: 2.54mm Box Header, Right Angle
							.XX	±0.05	批准		日期				Positions: 6~64
															Plastic Height: 8.8mm