





REV.	EQN. NO.	APPD.
A		

**Material:**

Insulator: Glass filled NY46 UL94V-0  
 Contacts: Brass / Phosphor Bronze T=0.25  
 Plating: Tin plated

**Electrical Characteristics:**

Contact Resistance: 20mΩmax. at DC 100mA  
 Insulator Resistance: 1000MΩmin. at 500V DC  
 Withstanding Voltage: 500V AC/rms 50Hz For 1 minute  
 Current Rating: 1 AMP  
 Operating Temperature: -40°C~+105°C



**Ordering Information:**

MTMR39-XX X X -22  
 M:Male  
 F:Female  
 S: Straight  
 R: Right  
 M: SMT  
 C: Cable

PINS	A	B	C
4	7.00	3.81	5.58
6	9.54	6.35	8.12
8	12.08	8.89	10.66
10	14.62	11.43	13.2
12	17.16	13.97	15.74
14	19.70	16.51	18.28
16	22.24	19.05	20.82
18	24.78	21.59	23.36
20	27.32	24.13	25.9
22	29.86	26.67	28.44
24	32.4	29.21	30.98
26	34.94	31.75	33.52

**MINTRON CO., LTD.**

TITLE: MICRO FEMALE SMT 無耳

.X ±0.20	X.° ±5°	UNITS mm
.XX ±0.10	.X° ±2°	MAT'L
.XXX ±0.05	.XX° ±1°	FINISH
	.XXX° ±0.5°	QTY
MICRO SOCKET CONNECTOR		

NAME (INTENDED USE)	PART NO. (INTENDED USE)
APPD: SUNNY	CHKD: USA
DR: ZOE	2006-11-28

DWG NO.: MTMR39-XXFM-22	SCALE: 1/1	SHEET: 1/1	REV: A
-------------------------	------------	------------	--------