



No. of Contacts	DIMENSIONS		
	DIM A	DIM B	DIM C
2P	4.25	1.25	7.55
3P	5.50	2.50	8.80
4P	6.75	3.75	10.05
5P	8.00	5.00	11.30
6P	9.25	6.25	12.55
7P	10.50	7.50	13.80
8P	11.75	8.75	15.05
9P	13.00	10.00	16.30

No. of Contacts	DIMENSIONS		
	DIM A	DIM B	DIM C
10P	14.25	11.25	17.55
11P	15.50	12.50	18.80
12P	16.75	13.75	20.05
13P	18.00	15.00	21.30
14P	19.25	16.25	22.55
15P	20.50	17.50	23.80
16P	21.75	18.75	25.05



PCB Layout

- 技术参数 SPECIFICATIONS
- ◆ 适用线规：AWG#28~#32
 - ◆ Applicable Wire: AWG#28~#32
 - ◆ 额定电压：125V DC,AC(rms)
 - ◆ Rated voltage: 125V DC,AC(rms)
 - ◆ 额定电流：1A
 - ◆ Rated Current: 1A
 - ◆ 耐压值：500V AC/minute
 - ◆ Withstand voltage: 500V AC/min.
 - ◆ 工作温度：-25°C ~ +85°C
 - ◆ Working Temp：-25°C ~ +85°C
 - ◆ 绝缘电阻：≥ 1000 MΩ
 - ◆ Insulation resistance: ≥ 1000 MΩ
 - ◆ 接触电阻：≤ 20mΩ
 - ◆ Contact resistance: ≤ 20mΩ

③	Solder Tab	—	2	Phosphor bronze	Ag-PLATED	—
②	PIN	—	—	Phosphor bronze	Ag-PLATED	—
①	Base	—	1	PA46	—	—
ITEM	PART NAME	TER/NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE	TITLE:	
DRAWN	JIANKUN.LIU	2015.03.17	FPC	
 ELECTRONICS CO.,LTD				

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.				
	A		NEW							
TOLERANCES ARE				30~±0.1	±0.30	ANGLE	PART NO.	1.25T-nP-WV	PROJ.	SHEET 1 OF 1
				10~±0.20	±0.20	ANGLE	PART NO.	1.25T-nP-WV	PROJ.	SHEET 1 OF 1
				5~±0.10	±0.15	±2'	DRAWING NO.			
				~5	±0.10					