



NOTES:

- 1.Specifications
- 1-1.INSERT FORCE:35N MAX.
- 1-2.WITHDRAW FORCE:10N MIN.INITIAL 8-20N AFTER
- 1-3.Current rating:1.0A
- 1-4.Voltage Rating:30V
- 1-5.Life Test:10000 CYCLES MIN.
- 1-6.:Dielectric withstanding:voltage100V AC MIN.
- 1-7.Contact resistance:30mΩ
- MAX.INITIAL;40mΩ MAX AFTER
- 1-8.Insulation resistance:100MΩ MIN
- 1-9.Temperature range:-30°TO +80°

APPROVALS		DATE		ELECTRONICS CO.,LTD		
DRAWN	D.J.LV	2017/12/26		HARDWARE		
CHECKED				TITLE: USB CONNECTOR		
APPROVALS				PART NO. U-A-24DD-W-1		
TOLERANCES ARE		30~11L ±0.30	ANGLE	UNIT: mm	SCALE: 1:1	PROJ: 1 OF 1
		10~30 ±0.20				
		5~10 ±0.15	±2°	DRAWING NO.		SHEET 1 OF 1
		~5 ±0.10				
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			