


- NOTES:
- Specifications
 - 1-1.INSERT FORCE:35N MAX.
 - 1-2.WITHDRAW FORCE:10N
 - MIN. INITIAL: 8-20N AFTER
 - 1-3.Current rating:1.0A
 - 1-4.Voltage Rating:30V
 - 1-5.Life Test:10000 CYCLES MIN.
 - 1-6.:Dielectric withstanding:voltage100V AC MIN.
 - 1-7.Contact resistance:30mΩ
 - MAX. INITIAL:40mΩ MAX AFTER
 - 1-8.Insulation resistance:100MΩ
 - 1-9.Temperature range:-30°TO +80°

RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm



APPROVALS		DATE	ELECTRONICS CO.,LTD	
DRAWN	D.J.L.V	2017/12/26		
CHECKED				
APPROVALS				
TITLE:		USB CONNECTOR	PART NO.	U-A-39DD-Y-1
APPROVALS		ANGLE	UNIT:	SCALE: 1:1
TOLERANCES ARE		±0.30	±0.20	±0.15
30°~以上		±0.30	±0.20	±0.15
10°~30		±0.20	±0.15	±0.10
5°~10		±0.15	±0.10	±0.05
~5		±0.10	±0.05	±0.02
DRAWING NO.			PROJ:	SHEET 1 OF 1

ECN NO.	REV.	DATE.	DESCRIPTION.
	A		NEW

CHANGE.	CHECK.	APPRO.