



NOTE:

1.MATERIAL:

a.HOUSING: PBT GLASS FIBRE UL94V-0;

b.CONTACT: BRASS T=0.25mm

c.SURFACE PLATING: Au1u"+Sn80-100u"+Ni60u")

d.SHEEL: SPCC-SD-DILED.T=0.3mm

<SURFACE PLATING: Cu50-80u"/Ni50-80u: _

2.ELECTRIC:

a.CONTACT RESISTANCE: 30 MILLIOHMS MAX

b.INSULATION RESISTANCE: 1000 MEGA DHMS MIN

c.DIELECTRIC VOLTAGE: 500V AC ONE MIN LEVEL

d.OPERATING TEMPERATURE: -55'-85'

| APPROVALS | | DATE | TITLE: | | | |
|----------------|-------|--------------|---------------------|---------------|--------|--------|
| DRAWN | D.JLV | 2018/1/12 | ELECTRONICS CO.,LTD | | | |
| CHECKED | | | A 公鱼义 | | | |
| APPROVALS | | | PART NO. | U-G-04WS-W-05 | SCALE: | 1:1 |
| TOLERANCES ARE | | 30~Ø以上 ±0.30 | ANGLE | | PROJ: | |
| | | 10~30 ±0.20 | UNIT: | mm | | |
| | | 5~10 ±0.15 | DRAWING NO. | | | |
| | | ~5 ±0.10 | | | SHEET | 1 OF 1 |
| ECN NO. | REV. | DATE. | DESCRIPTION. | CHANGE. | CHECK. | APPRO. |
| | A | | NEW | | | |